
Accessories

Accessories for drum and laboratory pump B 2 at a glance



- Hose clamp
- 8 Hose
- Drum adapter
- Emission proof drum adapter
- Foot strainer
- Wall bracket
- Lutz nozzle

Accessories

for drum and laboratory pump B1/B2 Battery and Lutz B2 Vario

Productdetail	Specification	Order-No.
	Set-accessories Comprises of: Lutz nozzle, 1.5 mtr. PVC hose 3/4", hose connection, hose clamps, wall bracket For pump Lutz B2 Vario PP-SL ø 32	0201-550
	Hose fitting for pump tube PP Comprises of: Lutz nozzle, 1.5 m PVC hose 3/4", hose connector with wing nut, hose clamps For pump tube B1/B2 Battery PP	0201-551
	Hose fitting for pump tube PVDF Comprises of: Nozzle PVDF, 1.5 m special chemical hose 3/4", hose connector with wing nut, hose clamps For pump tube B1/B2 Battery PVDF	0201-554
	Hose fitting for pump tube SS Comprises of: Nozzle SS/FEP, 1.5 m universal chemical hose 3/4", hose connector with wing nut, hose clamps For pump tube B1/B2 Battery stainless steel	0201-556
	Flow rate: Temperature of medium: Temperature of medium: Temperature of medium: Market Spout 8 Lutz nozzle PP For filling and transferring neutral and aggressive liquids. The liquid stream can be regulated by a turnlock fastener. Outlet spout 8 12 mm (conical). With suspension hook. Polypropylene (PP) housing. FPM (FPM) seals. Operating pressure: max. 1 bar at 20 °C max. 300 mPas Flow rate: max. 40 l/min. (water) Temperature of medium: max. 50 °C Weight: approx. 0.1 kg Connection: Hose liner DN 19 (3/4")	0201-215
Q	4 Hose clamp Stainless steel hose clamp to fix hoses at the pump outlet connection and accessories. Nominal diameter: Ear clamp DN 19 (3/4")	0301-257

Accessories

for drum and laboratory pump B1/B2 Battery and Lutz B2 Vario

Specification Order-No. Productdetail

9 Drum adapter PP

For fixing the pump B2 in the drum or container opening.

For pump tube:	For pump type:		
ø 32 mm	PP-SL 32	G 2 outer thread	0204-328
ø 32 mm	PP-SL 32	ø 56.7 mm	0208-009
ø 28 mm	SS-SL 28	ø 56.7 mm	0208-010
ø 32 mm	PP-SL 32	BCS 70 x 6	0208-027
ø 32 mm	PP-SL 32	BCS 56 x 4	0208-051
ø 28 mm	SS-SL 28	BCS 56 x 4	0208-050
ø 28 mm	SS-SL 28	BCS 70 x 6	0208-053



10 Emission proof drum adapter

To prevent emission of dangerous gases when using a drum pump, so protecting the operator, the environment and the drive motor from hazardous, aggressive gases and vapours. Two venting valves ensure pressure compensation between inside of the drum and surrounding atmosphere.

Connection for gas displacement pipe: G 3/8

Screw-in thread: G 2 outer thread

Seals: FPM

Material: For pump type: PP PP-SL 32

0204-251

0204-539

12 Foot strainer

Made of PP for mounting onto the pump foot. Keeps impurities away

from the rotating parts.

Material: For pump tube: PP Ø 32 mm

14 Wall bracket

For storage of drum and laboratory pump Lutz B2 Vario. This facility helps to protect pumps from damage and maintain their value.

For pump Lutz B2 Vario 0102-079



Electronical flow meter, TR series

For efficient flow rate measuring of various liquids.

Ease of handling, compact design, available in polypropylene (PP)

or polyvinylidenefluoride (PVDF).

 TR90-PP
 Connection G1
 0213-031

 TR90-PVDF
 Connection G1
 0213-041

Ting County Coun

Trolley for steel and plastic drums

For more details see separate flow meter leaflet.

Suitable for 200-litre drum, with 2 swivel castors and 2 fixed castors made of painted tubular steel frame,

with holder for nozzle, hose and cable

0371-030



Nozzles, hoses and hose connections 81-87.